

## OPTIONAL FEATURES FOR MODELS 20/70

### **USER SPECIFIED DISINFECTANT**

If a user would like to continue with their present disinfectant, we will test their product for chemical compatibility, reprogram our software for dilution changes if required and insure safeness with HUBSCRUB components.

### **PARTS CLEANING**

Push button switch illuminates when parts cleaning has been selected. Rotating spray system rotates only in the lower region to concentrate cleaning of parts such as foot rests, leg rests, rehab parts, cushions, etc that are contained in a user supplied basket or a HUBSCRUB basket.

### **PARTS BASKET**

Basket accommodates a number of parts. 5" high swivel caster wheels raise the basket off the floor for effective under spray cleaning and the concentrated focus of the rotating spray system. Dimensions; 21" X 17" X 11 1/8".

### **MAINTAIN HOT WATER**

Water temperature is maintained at 110F degrees to insure water stays at recommended temperature when the unit is idle

for up to two hours. Heating element is controlled by the processor and will shut off if sink is empty or the time allocation has exceeded 2 hours without use.

### **CUSTOM CHEMICAL COUPLINGS**

Separate couplings for chemical tubing and container cap provide ease of use and additional safety when replacing empty containers. (Set of five).

### **HUBSCRUB MAT AND TOWEL**

A 44" x 96" towel attaches to a similar size vinyl mat with Velcro for easy removing. Mat and towel are placed under door to collect water when the door is opened. Ideal for locations that require control of water and safety concerns in a traffic area. Easy removal of towel for washing and drying.

### **POWER DRY**

The HUBSCRUB Power Dry is designed to cut drying time by as much as 75%. The Power Dry provides gentle heat and high air velocity to help dry equipment quickly and thoroughly. In combination with HUBSCRUB's Drying Aid, drying time is substantially reduced to return equipment to a waiting user.